



# QT2 DEVICE

The QT2 Device takes the response experience to a new level of performance. Providing the same features as other RF clickers, the QT2 expands upon functionality by offering advanced capabilities such as a full QWERTY keypad and backlit screen for easy viewing. The QT2 provides the richest and most fulfilling response experience ever.

## SPECS

### ENCLOSURE

- Dimensions: 5.1" L x 2.98" W x .88" H - Grip Area .66 H (129mm L x 76mm W x 20mm H - Grip Area 16mm)
- Weight: 4.8 oz. (with batteries)
- Ergonomic, lightweight, compact format
- LCD screen with backlight for optimum viewing
- Durable, rugged case ensures maximum longevity under extreme conditions
- Accommodation for a lanyard included

### USER INPUT

- QWERTY Entry
- 56 Keys, Plastic Keys with reliable Metal Dome buttons. Laser etched graphics with Backlight.
- Supported Symbols . , ~ " ; : ! \ ? @ # \$ % ^ & \* ( ) \_ + - = / < > [ ] { } ? € £

### DISPLAY

- 57.1mm x 26.9mm viewable area
- Easy to read LCD Display
- Channel Number, Battery Life Indicator, Answer Choice, Response Confirmation

### POWER & POWER MANAGEMENT

- Two AAA batteries
- Average battery life is 6 to 12 months

### USER IDENTIFICATION

- Fixed device ID
- Setup is plug-and-play with TurningPoint

### RF TECHNOLOGY

- Up to 74 sessions can be running at one time in close proximity without interference
- Fully FCC, CE and Industry Canada certified

### RANGE

- Presentation Mode - Range for one RF Receiver is 200 feet (400 ft. coverage)
- Test Mode - Data is stored in nonvolatile memory until individual finishes test and uploads responses

### SUPPORTED PRODUCTS

- TurningPoint v.5.3 and higher
- TurningPoint Cloud
- Insight 360 v.2.3.2 and higher
- Flow v.1.7 and higher

### SUPPORTED RECEIVERS

- RF+ Receiver (RRRF-03) \*Only supported with receiver firmware version 3.7+
- RF Receiver (RRRF-04) \*Only supported with receiver firmware version 3.7+
- Long Range Receiver (RRLR-02)

## FUNCTIONALITY HIGHLIGHTS

### INPUT CAPABILITIES

Multiple Choice, Multiple Response, Numeric Response, Short Answer, True/False, Essay

### PARTICIPANT LIST CREATION

Automatically create participant lists with QT2 Device's user stored data or have participants log in to an existing list. Easily move from one session to another.

### SELF-PACED TESTING

Participants use QT2 Device to navigate to any question on the test or assignment and select a response. The QT2 Device has the largest storage capacity in the industry, storing all responses into nonvolatile memory to ensure data security and stability.

### SUCCESSFUL TRANSMISSION

Participants and presenters receive visual successful transmission notification.

## KEY FEATURES

- Full backlit QWERTY keypad with plastic laser etched keys and metal dome buttons.
- Large LCD screen and backlight
- Channel search
- Automatic input mode selection
- Letters, numbers and symbol support
- Participant ID submission with each response
- User feedback in both Presentation and Test mode
- Skip questions and return to questions at end of test
- Presenter can use real-time progress monitoring solution
- Presenter can display individual test results or a custom message to each participant
- Ergonomic and sleek casing

